

**SH 2 S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

**General ordering data**

Version	Busbar support, medium yellow, 130 °C, Width: 40 mm, V-0, KrG, when screwed in
Order No.	<a href="#">0641720000</a>
Type	SH 2 S
GTIN (EAN)	4008190166304
Qty.	10 pc(s).

**SH 2 S****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	35.5 mm	Depth (inches)	1.398 inch
Height	40 mm	Height (inches)	1.575 inch
Width	40 mm	Width (inches)	1.575 inch
Net weight	26.9 g		

**Temperatures**

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	KrG	Surface finish	all others
Colour	medium yellow	UL 94 flammability rating	V-0

**System specifications**

Version	For the mounting rails
---------	------------------------

**Additional technical data**

Type of mounting	when screwed in
------------------	-----------------

**Conductors for clamping (rated connection)**

Type of connection	Miscellaneous
--------------------	---------------

**General**

Number of poles	1	Surface finish	all others
-----------------	---	----------------	------------

**Classifications**

ETIM 6.0	EC001166	ETIM 7.0	EC001166
ETIM 8.0	EC001166	ETIM 9.0	EC001166
ECLASS 9.0	27-40-06-07	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-40-06-07	ECLASS 11.0	27-40-06-07
ECLASS 12.0	27-40-06-07	ECLASS 13.0	27-40-06-07
ECLASS 14.0	27-40-06-07		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

## SH 2 S

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures