

SKMU M75 MS SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|-----------------|--|
| Version | SKMU MS (brass locknut), Locknut, M 75, 7 mm, Brass |
| Order No. | 0930640008 |
| Type | SKMU M75 MS SC |
| GTIN (EAN) | 4032248976126 |
| Qty. | 5 pc(s). |
| Delivery status | This article will no longer be available in the future. |
| Available until | 2024-08-31 |

SKMU M75 MS SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|-------|-----------------|------------|
| Height | 7 mm | Height (inches) | 0.276 inch |
| Net weight | 149 g | | |

General information

| | | | |
|-----------------|-------|------------------|--------|
| AF size 1 | 90 mm | Cable glands | M 75 |
| External thread | M 75 | Halogen | No |
| Internal thread | M 75 | Length of thread | 7 mm |
| Material | Brass | Pitch of thread | 1.5 mm |
| Thickness | 7 mm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000940 | ETIM 7.0 | EC000940 |
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ECLASS 9.0 | 27-14-44-24 | ECLASS 9.1 | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |
| ECLASS 14.0 | 27-14-08-05 | | |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

SKMU M75 MS SC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

