


WHP 2.5-35N/10X3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

Version	End and partition plate for terminals, dark beige, Height: 65.5 mm, Width: 2 mm, V-0, Wemid
Order No.	1050200000
Type	WHP 2.5-35N/10X3
GTIN (EAN)	4008190139636
Qty.	20 pc(s).

WHP 2.5-35N/10X3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	46.5 mm	Depth (inches)	1.831 inch
Height	65.5 mm	Height (inches)	2.579 inch
Width	2 mm	Width (inches)	0.079 inch
Net weight	3.876 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

System specifications

Version	End and intermediate plate	Rail	TS 35
---------	----------------------------	------	-------

Additional technical data

Installation advice	Feed-through (bushing)	Snap-on	Yes
---------------------	------------------------	---------	-----

Dimensions

TS 35 offset	32 mm
--------------	-------

General

Installation advice	Feed-through (bushing)	Rail	TS 35
---------------------	------------------------	------	-------

Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.0	27-14-11-33	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-33	ECLASS 11.0	27-14-11-33
ECLASS 12.0	27-14-11-33	ECLASS 13.0	27-25-03-01
ECLASS 14.0	27-25-03-01		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

WHP 2.5-35N/10X3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Con-
formity

[Confirmation of Standards EN 45545-2_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)