


**AP VSSC4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

End plates (AP) for the VSSC product series in light blue and black

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | VSSC, End plate            |
| Order No.  | <a href="#">1063120000</a> |
| Type       | AP VSSC4                   |
| GTIN (EAN) | 4032248947560              |
| Qty.       | 50 pc(s).                  |

**AP VSSC4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 58.5 mm | Depth (inches)  | 2.303 inch |
| Height     | 76 mm   | Height (inches) | 2.992 inch |
| Width      | 1.5 mm  | Width (inches)  | 0.059 inch |
| Net weight | 0.9 g   |                 |            |

**Temperatures**

|                     |                |                       |             |
|---------------------|----------------|-----------------------|-------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 |
| Humidity            | 5...96 %       |                       |             |

**General data**

|                           |       |         |               |
|---------------------------|-------|---------|---------------|
| Colour                    | black | Design  | miscellaneous |
| UL 94 flammability rating | V-0   | Version | End plate     |

**Connection data**

|                    |                  |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000490    | ETIM 7.0    | EC000490    |
| ETIM 8.0    | EC000490    | ETIM 9.0    | EC000490    |
| ECLASS 9.1  | 27-13-92-90 | ECLASS 11.0 | 27-13-08-92 |
| ECLASS 12.0 | 27-17-90-90 | ECLASS 13.0 | 27-17-90-90 |

**Tender specification sheets**

|                    |                     |                     |                                |
|--------------------|---------------------|---------------------|--------------------------------|
| Long specification | End plate for VSSC4 | Short specification | End plate for VARITECTOR VSSC4 |
|--------------------|---------------------|---------------------|--------------------------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |