

ELS 6/30 MC NE WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

ELS MultiCard markers can be printed with a PrintJet, plotter or SMark printer. In particular, colour printing with PrintJet AVANCED allows the eye-catching identification marking of cables and terminal strips in many ways.

ELS 6/30 for use in the WKM 8/30 cable markers or in the EM8/30 group-tag carriers

ELS 7/40 for use in the SchT5S group-tag carriers

ELS 16/40 for use in the WKM 18/43 cable markers or the SchT5 group-tag carriers

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|--------------------|--|
| Version | ELS, Insert markers, 30 x 6 mm, white |
| Order No. | 1045570000 |
| Type | ELS 6/30 MC NE WS |
| GTIN (EAN) | 4032248779475 |
| Qty. | 80 pc(s). |
| compatible printer | 2715590000 2438520000 2438510000 |

ELS 6/30 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.8 mm | Depth (inches) | 0.031 inch |
| Height | 30 mm | Height (inches) | 1.181 inch |
| Width | 6 mm | Width (inches) | 0.236 inch |
| Net weight | 1.1 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

General data

| | | |
|--|------------------------------|-----------|
| Colour | white | |
| Halogen | No | |
| Material | Polyamide 66 | |
| Material colour according to resistance code | 9 | |
| Number of markers per combination | 1 MultiCard = Insert markers | |
| Number of markers per packaging unit | Form of supply | MultiCard |
| Number per sheet | 16 | |
| Operating temperature range | -40...100 °C | |
| Operating temperature range, max. | 100 °C | |
| Operating temperature range, min. | -40 °C | |
| UL 94 flammability rating | V-2 | |
| Width | 6 mm | |

Conductor and cable markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads


| | |
|-----------------------------|--|
| Engineering Data | CAD data – STEP |
| Engineering Data | Zuken E3.S |
| Product Change Notification | Technical change to MultiCard material - DE Technical change to MultiCard material - EN MultiCard Material modification MultiCard Material Modifikation |
| Catalogues | Catalogues in PDF-format |

ELS 6/30 MC NE WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



ELS 6/30 MC NE WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

WKM for inlay tags



The halogen-free, transparent pocket of the WKM offers outstanding protection against environmental influences. Thanks to firm fixation with cable ties, it is suitable for almost all wire cross-sections.

The pre-printed tags are simply inserted into the WKM holder and secured with a clip. WKM cable markers are the right solution for maximum efficiency in on-site marking.

Your advantage when using WKM cables

- Paper and polyester labels can be printed individually with conventional office printers
- The robust design in combination with MultiCard ELS tags guarantees maximum protection against environmental influences

General ordering data

| | | |
|------------|----------------------------|---|
| Type | WKM 8/30 | Version |
| Order No. | 1631910000 | WKM, Conductor and cable markers, 7 - 115 mm, 30 x 8 mm, Wire |
| GTIN (EAN) | 4008190206666 | and cable markers, Transparent |
| Qty. | 50 pc(s). | |

EM 8/30 end bracket marker



The EM 8/30 end bracket marker is suitable for labelling the WEW 35/2 and ZEW 35/2 end brackets and can also be used as a group tag carrier for W-series terminals. The EM 8/30 can hold ESO 7/ESO 7P inlay tags. The pocket reliably protects the printing against environmental influences.

Inlay tags can be found under "Accessories".

General ordering data

| | | |
|------------|----------------------------|---|
| Type | EM 8/30 | Version |
| Order No. | 1806120000 | EM, Terminal marker, 32.4 x 7.2 mm, Pitch in mm (P): 7.20 |
| GTIN (EAN) | 4032248275298 | Weidmueller, Transparent |
| Qty. | 50 pc(s). | |