

WQV 70/95/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

Version	Cross-connector (terminal), when screwed in, Number of poles: 2, Pitch in mm (P): 27.00, Insulated: No, 232 A, Silver grey
Order No.	1063500000
Type	WQV 70/95/2
GTIN (EAN)	4008190028329
Qty.	5 pc(s).

WQV 70/95/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	61.6 mm	Depth (inches)	2.425 inch
Height	37 mm	Height (inches)	1.457 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	101.6 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

Conductors for clamping (rated connection)

Tightening torque, max.	3 Nm
-------------------------	------

Cross-connector

Number of cross-connected terminals	2	Rated current, 2-pole	232 A
Rated current, multi-pole	192 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	27 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

Rating data

Rated current	232 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

WQV 70/95/2

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
User Documentation	StorageConditionsTerminalBlocks Instruction
Catalogues	Catalogues in PDF-format
Brochures	

WQV 70/95/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Cutting and notching tools for cross-connections



- for Weidmüller Z-Series cross-connections
- for cross-connections from WQV 2.5 to WQV 35
- for cross-connection window of the terminal WSI 6

General ordering data

Type	WAW 1 NEUTRAL	Version
Order No.	9004500000	Miscellaneous tools
GTIN (EAN)	4008190053925	
Qty.	1 pc(s).	