

**WSD 2.5/SCAN WTR2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

The component plug is used to integrate an electrical component in a disconnect terminal block. After soldering the electronic component, the plug can be integrated into the disconnection area of our disconnect terminal blocks and thus changes the disconnect terminal block into a modular terminal block with integrated electronic component.

**General ordering data**

Version	Component plug (terminal), Plug-in connection, Plugged, dark beige
Order No.	<a href="#">1058760000</a>
Type	WSD 2.5/SCAN WTR2.5
GTIN (EAN)	4008190028398
Qty.	25 pc(s).

## WSD 2.5/SCAN WTR2.5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	29.58 mm	Depth (inches)	1.165 inch
Height	38.4 mm	Height (inches)	1.512 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	3.68 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

## Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

## System specifications

Version	Diode module	End cover plate required	No
Number of levels	1	PE connection	No

## Additional technical data

Explosion-tested version	No	Type of mounting	Plugged
--------------------------	----	------------------	---------

## CSA rating data

Certificate No. (CSA)	154685-1152890
-----------------------	----------------

## Conductors for clamping (rated connection)

Connection direction	top	Type of connection	Plug-in connection
----------------------	-----	--------------------	--------------------

## UL rating data

Certificate No. (UR)	E60693
----------------------	--------

## Classifications

ETIM 6.0	EC002018	ETIM 7.0	EC002018
ETIM 8.0	EC002018	ETIM 9.0	EC002018
ECLASS 9.0	27-14-11-49	ECLASS 9.1	27-14-11-49
ECLASS 10.0	27-14-11-49	ECLASS 11.0	27-14-11-49
ECLASS 12.0	27-14-11-49	ECLASS 13.0	27-25-03-05

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693

### WSD 2.5/SCAN WTR2.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**WSD 2.5/SCAN WTR2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Marker holder**

The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

**General ordering data**

Type	BZT 1 WS 10/5	Version
Order No.	<a href="#">1805490000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270231	
Qty.	100 pc(s).	
Type	BZT 1 ZA WS 10/5	Version
Order No.	<a href="#">1805520000</a>	Accessories, Marker holder
GTIN (EAN)	4032248270248	
Qty.	100 pc(s).	