

**SM 27/18 K MC NE GR****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labelling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | SwitchMark, Device markers, 18 x 27 mm, grey                                     |
| Order No.          | <a href="#">1073340000</a>   |
| Type               | SM 27/18 K MC NE GR  |
| GTIN (EAN)         | 4032248831425  |
| Qty.               | 80 pc(s).  |
| compatible printer | <a href="#">2715590000</a> <a href="#">2438520000</a> <a href="#">2438510000</a> |

## SM 27/18 K MC NE GR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 1 mm    | Depth (inches)  | 0.039 inch |
| Height     | 18 mm   | Height (inches) | 0.709 inch |
| Width      | 27 mm   | Width (inches)  | 1.063 inch |
| Net weight | 1.488 g |                 |            |

## Temperatures

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -40...60 °C |
|-----------------------------|-------------|

## General data

|  |                              |           |
|--|------------------------------|-----------|
| Adhesive                                     | Double-sided adhesive tape   |           |
| Colour                                       | grey                         |           |
| Halogen                                      | No                           |           |
| Material                                     | Polyamide 66                 |           |
| Material colour according to resistance code | 8                            |           |
| Number of markers per combination            | 1 MultiCard = Device markers |           |
| Number of markers per packaging unit         | Form of supply               | MultiCard |
| Operating temperature range                  | -40...60 °C                  |           |
| Operating temperature range, max.            | 60 °C                        |           |
| Operating temperature range, min.            | -40 °C                       |           |
| UL 94 flammability rating                    | V-2                          |           |
| Version                                      | Self-adhesive                |           |
| Width  | 27 mm                        |           |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 |             |             |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Product Change Notification | <a href="#">MultiCard Material modification</a><br><a href="#">MultiCard Material Modifikation</a> |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                   |  |

Creation date August 29, 2024 1:32:41 AM CEST

Catalogue status 17.08.2024 / We reserve the right to make technical changes.

### SM 27/18 K MC NE GR

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



## SM 27/18 K MC NE GR

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Complementary products



SM is a MultiCard marker for labelling control and signalling devices. The tags are clipped into the carriers or attached by means of the adhesive film already fitted to them. Customised tags can be created with the PrintJet CONNECT or Plotter marking systems.

- Users can quickly produce tags to suit their needs
- No need to stock expensive standard tags
- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- For extreme demands, we recommend the ETO SM protective film
- Holders can be used for the 22-mm or 30-mm-diameter push-buttons from Siemens, ABB, Moeller and Télémécanique

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |   |
|------------|----------------------------|---|
| Type       | ETO SM 27/18 TRANSPAR.     | Version   |
| Order No.  | <a href="#">1720590002</a> | SwitchMark, Protective cap, 18 x 27 mm, Transparent |
| GTIN (EAN) | 4008190988005              |   |
| Qty.       | 10 pc(s).                  |   |