

**WBB WDK2.5/BL5.08****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Fixing brackets for our pluggable terminal blocks serve as mechanical fasteners for the respective plugs. They protect both the connector and the contact from mechanical stress and unintentional loosening due to vibration.

**General ordering data**

Version	Partition plate (terminal), End and intermediate plate, 58 mm x 45.2 mm, orange
Order No.	<a href="#">1072660000</a>
Type	WBB WDK2.5/BL5.08
GTIN (EAN)	4008190470555
Qty.	10 pc(s).

## WBB WDK2.5/BL5.08

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	45.2 mm	Depth (inches)	1.78 inch
Height	58 mm	Height (inches)	2.283 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	8.5 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

## Material data

Material	PA 66	Colour	orange
UL 94 flammability rating	V-2		

## System specifications

Version	End and intermediate plate
---------	----------------------------

## Additional technical data

Installation advice	Direct mounting	Snap-on	No
---------------------	-----------------	---------	----

## General

Installation advice	Direct mounting
---------------------	-----------------

## Classifications

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-33
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	936a8f21-8ce1-4838-a60e-9ad69268c052

## Approvals

ROHS	Conform
------	---------

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	