

CC 85/54 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



ClipCard device markers in MultiCard format are used for labelling electrical installations and switchgear systems, and offer an interesting alternative to engraving. Thanks to the proven MultiCard format, labelling is possible with PrintJet CONNECT or Plotter.

- Highly resistant printing quality when using the PrintJet as a substitute for engraving
- Universal fixing
- Carrier (screwable or with cable ties)
- Tag rail (self-adhesive or screw fixing)
- Or self-adhesive tags

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Version	ClipCard, Device markers, 54 x 85 mm, Holder Logimark-H, To customer specification
Order No.	1138460000
Type	CC 85/54 MC SDR
GTIN (EAN)	4032248919918
Qty.	2 pc(s).
compatible printer	2715590000 2438520000 2438510000

CC 85/54 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	0.8 mm	Depth (inches)	0.031 inch
Height	54 mm	Height (inches)	2.126 inch
Width	85 mm	Width (inches)	3.346 inch
Net weight	9 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

General data

Application/manufacturer	Holder Logimark-H	
Colour	To customer specification	
Colour of printing	black	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Device markers	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40...100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Printed characters	Based on customer requirements (Please send M-Print PRO file)	
Printing method	MC Laser	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Width	85 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CC 85/54 MC SDR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings



CC 85/54 MC SDR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****General ordering data**

Type	CC-H 85/54 SW	Version
Order No.	1631640001	ClipCard, Accessories, 90 x 58 mm, black
GTIN (EAN)	4008190465254	
Qty.	20 pc(s).	
Type	CC-H 85/54 GR	Version
Order No.	1631640002	ClipCard, Accessories, 90 x 58 mm, grey
GTIN (EAN)	4008190465261	
Qty.	20 pc(s).	
Type	CC-H 85/54 BG	Version
Order No.	1631640003	ClipCard, Accessories, 90 x 58 mm, dark beige
GTIN (EAN)	4008190465292	
Qty.	20 pc(s).	
Type	CC-HO 85/54 SW	Version
Order No.	1603290000	ClipCard, Accessories, 90 x 58 mm, black
GTIN (EAN)	4008190188306	
Qty.	20 pc(s).	