

**BZT PRV16 SW 35X15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The marker holder offer the possibility of additional marker mounting. Depending on the design, the respective levels of the PRV and PPV terminal blocks can be labeled with the corresponding marker.

**General ordering data**

Version	P-series, Marker holder, black, Number of levels: 16, TS 35 x 15
Order No.	<a href="#">1173540000</a>
Type	BZT PRV16 SW 35X15
GTIN (EAN)	4032248965885
Qty.	20 pc(s).

**BZT PRV16 SW 35X15****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	113.4 mm	Depth (inches)	4.465 inch
Height	225 mm	Height (inches)	8.858 inch
Width	10.2 mm	Width (inches)	0.402 inch
Net weight	52.7 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	125 °C		

**Material data**

Material	Polycarbonate	Colour	black
UL 94 flammability rating	V-0		

**System specifications**

Version	For the mounting rails	Number of levels	16
Number of clamping points per level	2	Rail	TS 35 x 15

**Conductors for clamping (rated connection)**

Number of connections	32
-----------------------	----

**General**

Rail	TS 35 x 15
------	------------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-14-11-92

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	