

SAI-M23-KS-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Empty enclosure
Order No.	1170270000
Type	SAI-M23-KS-L-7/12
GTIN (EAN)	4032248962259
Qty.	1 pc(s).

SAI-M23-KS-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	82 g
------------	------

Technical data customisable plug-in connectors

Cable diameter, max.	12 mm	Cable diameter, min.	7 mm
Housing main material	Copper-zinc alloy	Plugging cycles	> 1000
Pollution severity	3	Protection degree	IP67, IP69K
Shield connection	Yes	Temperature range of housing	-40...+125 °C

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC003556
ETIM 8.0	EC003556	ETIM 9.0	EC003556
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-24
ECLASS 11.0	27-44-02-24	ECLASS 12.0	27-44-02-24
ECLASS 13.0	27-44-02-24	ECLASS 14.0	27-44-02-24

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	1c533b66-fcff-4da5-b89f-fd55fbf5cb55
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-M23-KS-L-7/12

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Dimensioned drawing



SAI-M23-KS-L-7/12**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Inserts without contacts**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Type	SAI-M23-SE-L-4/4	Version
Order No.	1170380000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962518	
Qty.	1 pc(s).	
Type	SAI-M23-BE-L-6	Version
Order No.	1170370000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962266	
Qty.	1 pc(s).	
Type	SAI-M23-BE-L-4/4	Version
Order No.	1995810000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248925674	
Qty.	1 pc(s).	
Type	SAI-M23-SE-L-6	Version
Order No.	1170350000	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962303	
Qty.	1 pc(s).	

Cable connector

