

**KLBUE 10-20 FM4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image**

Similar to illustration

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the TS 35 DIN rail. The shield is diverted from the shield clamping saddles via the mounting foot to the TS 35 mounting rail and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Clamping yoke for shield connection
Order No.	<a href="#">1252510000</a>
Type	KLBUE 10-20 FM4
GTIN (EAN)	4032248112555
Qty.	10 pc(s).

**KLBUE 10-20 FM4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	50.5 mm	Height (inches)	1.988 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	36.9 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., max.	130 °C
---------------------	----------------	----------------------------------	--------

**Material data**

Colour	silver
--------	--------

**System specifications**

Rail	TS 35
------	-------

**Additional technical data**

Explosion-tested version	No	Installation advice	TS 35
Type of mounting	Snap-on		

**Conductors for clamping (rated connection)**

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
Type of connection	Spring connection		

**General**

Installation advice	TS 35	Rail	TS 35
---------------------	-------	------	-------

**Classifications**

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20
ECLASS 14.0	27-25-01-20		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

### KLBUE 10-20 FM4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	