

**KTB RNHD 453820 R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Rain Covers**

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.

**General ordering data**

|                     |  |
|---------------------|--|
| Version             | Klippon TB (Terminal Box), Rain hood, Height: 55.9 mm, Width: 387 mm, Depth: 211.2 mm, Material: Stainless steel 1.4301, Mirror polished, silver |
| Order No.           | <a href="#">1281460000</a>   |
| Type                | KTB RNHD 453820 R  |
| GTIN (EAN)          | 4050118072228  |
| Qty.                | 1 pc(s).   |
| Delivery status     | <b>This article will no longer be available in the future.</b>   |
| Available until     | 2024-08-31   |
| Alternative product | <a href="#">1314200000</a>   |

Creation date November 7, 2024 9:43:11 AM CET

Catalogue status 26.10.2024 / We reserve the right to make technical changes.

**KTB RNHD 453820 R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 211.2 mm | Depth (inches)  | 8.315 inch  |
| Height     | 55.9 mm  | Height (inches) | 2.201 inch  |
| Width      | 387 mm   | Width (inches)  | 15.236 inch |
| Net weight | 2,040 g  |                 |             |

**General information**

|          |                        |                |                 |
|----------|------------------------|----------------|-----------------|
| Material | Stainless steel 1.4301 | Surface finish | Mirror polished |
|----------|------------------------|----------------|-----------------|

**General information on accessories**

|          |                        |                |                 |
|----------|------------------------|----------------|-----------------|
| Material | Stainless steel 1.4301 | Surface finish | Mirror polished |
|----------|------------------------|----------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000744    | ETIM 7.0    | EC000744    |
| ETIM 8.0    | EC000744    | ETIM 9.0    | EC000744    |
| ECLASS 9.0  | 27-18-24-05 | ECLASS 9.1  | 27-18-92-90 |
| ECLASS 10.0 | 27-18-24-05 | ECLASS 11.0 | 27-18-24-05 |
| ECLASS 12.0 | 27-18-24-05 | ECLASS 13.0 | 27-18-24-05 |
| ECLASS 14.0 | 27-18-24-05 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |  |
|--------------------|--|
| Engineering Data   | <a href="#">CAD data – STEP</a>          |
| User Documentation | <a href="#">INSTR KTB RNHD R</a>         |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |
| Brochures          |  |