

ETA 1180 01 4A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Weidmueller offer circuit breakers for the integration of our fuse terminals for automotive fuses with a range from 100 mA to 25 A.

General ordering data

| | |
|------------|----------------------------|
| Version | Miniature fuse, 4 A |
| Order No. | 1279020000 |
| Type | ETA 1180 01 4A |
| GTIN (EAN) | 4050118091496 |
| Qty. | 5 pc(s). |

ETA 1180 01 4A**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|------------|
| Depth | 52.3 mm | Depth (inches) | 2.059 inch |
| Height | 24.4 mm | Height (inches) | 0.961 inch |
| Width | 8.2 mm | Width (inches) | 0.323 inch |
| Net weight | 10.6 g | | |

Material data

| | |
|--------|-------|
| Colour | black |
|--------|-------|

System specifications

| | |
|---------|----------------|
| Version | Fuse cartridge |
|---------|----------------|

Additional technical data

| | | | |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Plugged |
|---------------------|-----------------|------------------|---------|

Fuse cartridges

| | | | |
|---------|----------------|---------|-----|
| Colour | black | Current | 4 A |
| Version | Fuse cartridge | | |

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Rating data

| | | | |
|---------------|------|---------------|-----|
| Rated voltage | 64 V | Rated current | 4 A |
|---------------|------|---------------|-----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000035 | ETIM 7.0 | EC000035 |
| ETIM 8.0 | EC002704 | ETIM 9.0 | EC002704 |
| ECLASS 9.0 | 27-14-20-01 | ECLASS 9.1 | 27-14-20-01 |
| ECLASS 10.0 | 27-14-20-01 | ECLASS 11.0 | 27-14-20-01 |
| ECLASS 12.0 | 27-14-20-01 | ECLASS 13.0 | 27-14-20-01 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |