

**THM MT30X 8/8 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

|                    |   |
|--------------------|---|
| Version            | THM, Device markers, 8 x 8 mm, yellow                 |
| Order No.          | <a href="#">1310540000</a>                            |
| Type               | THM MT30X 8/8 GE                                      |
| GTIN (EAN)         | 4050118112665   |
| Qty.               | 1 pc(s).  |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

**THM MT30X 8/8 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.003 inch |
| Height     | 8 mm    | Height (inches) | 0.315 inch |
| Width      | 8 mm    | Width (inches)  | 0.315 inch |
| Net weight | 158 g   |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

**General data**

|                                      |                               |            |
|--------------------------------------|-------------------------------|------------|
| Adhesive                             | Acrylate                      |            |
| Colour                               | yellow                        |            |
| Halogen                              | No                            |            |
| Material                             | Polyester                     |            |
| Number of markers per combination    | 1 Label reel = Device markers |            |
| Number of markers per packaging unit | Form of supply                | Label reel |
| Number per roll                      | 10,000                        |            |
| Operating temperature range          | -40... 150 °C                 |            |
| Operating temperature range, max.    | 150 °C                        |            |
| Operating temperature range, min.    | -40 °C                        |            |
| Printing method                      | Thermal transfer              |            |
| UL 94 flammability rating            | V-0                           |            |
| Version                              | Self-adhesive, halogen-free   |            |
| Width                                | 8 mm                          |            |

**Device markers**

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ETIM 9.0    | EC001288    |
| ECLASS 9.0  | 27-40-06-29 | ECLASS 9.1  | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |
| ECLASS 14.0 | 27-28-11-04 |             |             |

**Environmental Product Compliance**

|                        |                             |
|------------------------|-----------------------------|
| REACH SVHC             | /                           |
| RoHS Compliance Status | Compliant without exemption |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

**THM MT30X 8/8 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**THM MT30X 8/8 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM 110/360 SW       | Version    |
| Order No.  | <a href="#">2005070000</a> | Ink ribbon |
| GTIN (EAN) | 4050118390049              |            |
| Qty.       | 1 pc(s).                   |            |