

**KTB RNHD 484820 S4E R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Abbildung ähnlich

**Integrate, expand and customise: The ideal expansion for every application**

The consistent structure of accessories for the new Klippon® TB enclosure range means that you can easily adapt the enclosure to the specific requirements of each application.

**Rain Covers**

The rain cover provides an ideal, additional level of protection for the enclosure if it is installed in unusual climatic zones with, for instance, very heavy rainfall or extreme levels of direct sunlight.

**General ordering data**

|            |   |
|------------|---|
| Version    | Klippon TB (Terminal Box), Rain hood, Height: 55.9 mm, Width: 485 mm, Depth: 211.2 mm, Material: Stainless steel 1.4404 (316L), electropolished, silver |
| Order No.  | <a href="#">1314230000</a>  |
| Type       | KTB RNHD 484820 S4E R   |
| GTIN (EAN) | 4050118117349   |
| Qty.       | 1 pc(s).  |

**KTB RNHD 484820 S4E R****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 211.2 mm | Depth (inches)  | 8.315 inch  |
| Height     | 55.9 mm  | Height (inches) | 2.201 inch  |
| Width      | 485 mm   | Width (inches)  | 19.094 inch |
| Net weight | 3,340 g  |                 |             |

**General information**

|          |                                  |                |                 |
|----------|----------------------------------|----------------|-----------------|
| Material | Stainless steel 1.4404<br>(316L) | Surface finish | electropolished |
|----------|----------------------------------|----------------|-----------------|

**General information on accessories**

|          |                                  |                |                 |
|----------|----------------------------------|----------------|-----------------|
| Material | Stainless steel 1.4404<br>(316L) | Surface finish | electropolished |
|----------|----------------------------------|----------------|-----------------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000744    | ETIM 7.0    | EC000744    |
| ETIM 8.0    | EC000744    | ETIM 9.0    | EC000744    |
| ECLASS 9.0  | 27-18-24-05 | ECLASS 9.1  | 27-18-92-90 |
| ECLASS 10.0 | 27-18-24-05 | ECLASS 11.0 | 27-18-24-05 |
| ECLASS 12.0 | 27-18-24-05 | ECLASS 13.0 | 27-18-24-05 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |  |
|--------------------|--|
| User Documentation | <a href="#">INSTR KTB RNHD R</a>         |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |
| Brochures          |  |