

**PAC-S1200-RV24-V0-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |  |
|------------|--|
| Version    | Pre-assembled cable, PAC, Cable LiYY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">1329140030</a>                                 |
| Type       | PAC-S1200-RV24-V0-3M                                       |
| GTIN (EAN) | 4099986577879  |
| Qty.       | 1 pc(s).   |

**PAC-S1200-RV24-V0-3M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 482 g |
|------------|-------|

**General Data**

|                    |  |                       |                             |
|--------------------|--|-----------------------|-----------------------------|
| Cable              | Cable LiYY                                     | Cable length          | 3 m                         |
| Connector PLC side | 4 x SIEMENS S71200<br>6ES7292-1AG30-0XA0<br>7P | Interface connector   | WEIDMUELLER RSV 24P<br>MALE |
| Material           | PVC  | Number of poles, min. | 24-pole                     |
| Outer diameter     | 9.2 ± 1 mm                                     | Suitable for          | Digital signals             |
| Wire cross-section | 0.25 mm <sup>2</sup>                           |                       |                             |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ECLASS 9.0  | 27-24-22-20 | ECLASS 9.1  | 27-24-22-20 |
| ECLASS 10.0 | 27-24-22-20 | ECLASS 11.0 | 27-24-22-20 |
| ECLASS 12.0 | 27-24-22-20 | ECLASS 13.0 | 27-24-22-20 |
| ECLASS 14.0 | 27-24-22-20 |             |             |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |
| RoHS Compliance Status | Compliant                            |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|