

HDC HP 250 M CM3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Version	HDC insert, Pin, Crimp connection
Order No.	1415410000
Type	HDC HP 250 M CM3
GTIN (EAN)	4050118216370
Qty.	1 pc(s).

HDC HP 250 M CM3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	41.21 g
------------	---------

General data

Colour	black	Free from halogens	false
Material	Copper alloy	Type	Pin
Type of connection	Crimp connection		

Version

Material	Copper alloy	Type of connection	Crimp connection
----------	--------------	--------------------	------------------

Classifications

ETIM 6.0	EC000796	ETIM 7.0	EC000796
ETIM 8.0	EC000796	ETIM 9.0	EC000796
ECLASS 9.0	27-44-02-04	ECLASS 9.1	27-44-02-04
ECLASS 10.0	27-44-02-04	ECLASS 11.0	27-44-02-04
ECLASS 12.0	27-44-02-04	ECLASS 13.0	27-44-02-04
ECLASS 14.0	27-44-02-04		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c

Important note

Product information	Depending on the intended operation, internally generated voltages can superimpose the working voltage and contain corresponding peaks. It is imperative to ensure that these peak voltages do not exceed the rated voltage. For applications outside of this specification, please contact us.
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	1487780000_00_11_13_BPZ_HDC_HP250-550_web.pdf
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC HP 250 M CM3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Crimp contacts CM3



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC-C-M3-SM1.5AG	Version
Order No.	1698120000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190885038	section, max.: 1.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM2.5AG	Version
Order No.	1698140000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190885052	section, max.: 2.5, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM4.0AG	Version
Order No.	1682260000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190473990	section, max.: 4, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM6.0AG	Version
Order No.	1682280000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190474010	section, max.: 6, turned, Copper alloy
Qty.	100 pc(s).	
Type	HDC-C-M3-SM10.0AG	Version
Order No.	1682300000	Heavy-duty connectors, Crimp contact, CM 3, Pin, Conductor cross-
GTIN (EAN)	4008190474034	section, max.: 10, turned, Copper alloy
Qty.	100 pc(s).	