

GZ 5.0A/F**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

For protection against overcurrent, we offer cartridge fuse with dimensions 6.3x32 mm in sizes from 500 mA to 12.5 A.

General ordering data

Version	Miniature fuse, quick-acting, 5 A, G-Si. 6.3 x 32
Order No.	1460620000
Type	GZ 5.0A/F
GTIN (EAN)	4050118266610
Qty.	10 pc(s).

GZ 5.0A/F

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6.3 mm	Depth (inches)	0.248 inch
Height	32 mm	Height (inches)	1.26 inch
Width	6.3 mm	Width (inches)	0.248 inch
Net weight	2.4 g		

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Additional technical data

Installation advice	Direct mounting	Type of mounting	Plugged
---------------------	-----------------	------------------	---------

Fuse cartridges

Cartridge fuse	G-Si. 6.3 x 32	Characteristics	quick-acting
Colour	Light Grey	Current	5 A
Melting integral	40 A ² s	Optical function display	No
Power output (@ 1.5 In)	2.9 W	Rated breaking capacity	50 kA
Version	Fuse accessories	Voltage drop	150 mV

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated voltage	500 V	Rated current	5 A
---------------	-------	---------------	-----

Classifications

ETIM 6.0	EC000035	ETIM 7.0	EC000035
ETIM 8.0	EC002704	ETIM 9.0	EC002704
ECLASS 9.0	27-14-20-01	ECLASS 9.1	27-14-20-01
ECLASS 10.0	27-14-20-01	ECLASS 11.0	27-14-20-01
ECLASS 12.0	27-14-20-01	ECLASS 13.0	27-14-20-01

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Creation date July 15, 2024 2:00:24 AM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.