

**DMS PRO SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Only for Europe



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Version	Mounting tool
Order No.	<a href="#">1479090000</a>
Type	DMS PRO SET
GTIN (EAN)	4050118286786
Qty.	1 pc(s).

## DMS PRO SET

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	261 mm	Depth (inches)	10.276 inch
Width	338 mm	Width (inches)	13.307 inch
Net weight	2,278 g		

## Technical data

Charging time	Description of article	Mains-operated torque screwdriver with 1/4" drive
30 min		

## Electric screwdriver

Battery voltage	3.6 V	Bit holder	1/4" DIN 3126 Form E6.3
Charger input	AC 220-240V~50-60Hz 30W	Charger output	DC 2.8...6V; 4.8A / 30W max.
Charging time	30 min	Idling speed	200 u. 600 min <sup>-1</sup>
Rated voltage	3.6 V	Rechargeable batteries	Li-Ion battery
Torque setting, max.	3 Nm	Torque setting, min.	0.36 Nm

## Screwing tools

Torque setting, max.	3 Nm	Torque setting, min.	0.36 Nm
----------------------	------	----------------------	---------

## Classifications

ETIM 6.0	EC001395	ETIM 7.0	EC001395
ETIM 8.0	EC001395	ETIM 9.0	EC001395
ECLASS 9.0	21-05-21-90	ECLASS 9.1	21-04-04-17
ECLASS 10.0	21-05-21-90	ECLASS 11.0	21-05-08-90
ECLASS 12.0	21-05-08-90	ECLASS 13.0	21-05-08-90

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## DMS PRO SET

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings


### Example of use



### Example of use



### Example of use



## DMS PRO SET

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## DMS PRO



Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

## General ordering data

Type	AKKU DMS PRO	Version
Order No.	<a href="#">1479110000</a>	Mounting tool
GTIN (EAN)	4050118348712	
Qty.	1 pc(s).	
Type	DMS PRO	Version
Order No.	<a href="#">1479120000</a>	Mounting tool
GTIN (EAN)	4050118287011	
Qty.	1 pc(s).	
Type	LG DMS PRO/ DMS 3	Version
Order No.	<a href="#">9007460000</a>	DMS 3, 90 % bei 3x 500 V AC / > 91 % bei 3 x 400 V AC
GTIN (EAN)	4008190404970	
Qty.	1 pc(s).	

## E6.3 bits - Phillips / recess

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits are Phillips-Recessed type PH/DIN 5260.  
1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 PH1X70	Version
Order No.	<a href="#">9024080000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870744	
Qty.	5 pc(s).	
Type	BIT E6,3 PH2X70	Version
Order No.	<a href="#">9024090000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870720	
Qty.	5 pc(s).	

## DMS PRO SET

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Bit assortment, E6.3

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection



## General ordering data

Type	BIT-BOX WI DMS 3	Version
Order No.	<a href="#">9024970000</a>	Accessories, Mounting tool
GTIN (EAN)	4032248068067	
Qty.	1 pc(s).	

## BE6.3 bits - slotted

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126



## General ordering data

Type	BIT E6,3 1,2X6,5X70	Version
Order No.	<a href="#">9020740000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504718	
Qty.	5 pc(s).	
Type	BIT E6,3 0,8X4,0X70	Version
Order No.	<a href="#">9024030000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852658	
Qty.	5 pc(s).	
Type	BIT E6,3 0,4X2,5X70	Version
Order No.	<a href="#">9020750000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4032248504725	
Qty.	5 pc(s).	
Type	BIT E6,3 Z 0,8X4,0X39	Version
Order No.	<a href="#">9025590000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190151935	
Qty.	10 pc(s).	
Type	BIT E6,3 0,6X3,5X70	Version
Order No.	<a href="#">9024020000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852627	
Qty.	5 pc(s).	

Creation date June 4, 2024 9:00:44 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

**DMS PRO SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

Type	BIT E6,3 1,0X5,5X70	Version
Order No.	<a href="#">9024040000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852665	
Qty.	5 pc(s).	
Type	BIT E6,3 0,5X3,0X70	Version
Order No.	<a href="#">9024000000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190852634	
Qty.	5 pc(s).	

**E6.3 bits - Pozidriv / Supadriv**

1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection  
Crosshead bits Pozidriv PZ/DIN 5262, 1/4" drive, E 6.3  
DIN 3126

**General ordering data**

Type	BIT E6,3 PZ2X70	Version
Order No.	<a href="#">9024110000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870706	
Qty.	5 pc(s).	
Type	BIT E6,3 PZ1X70	Version
Order No.	<a href="#">9024100000</a>	Accessories, Screwdriver insert
GTIN (EAN)	4008190870713	
Qty.	5 pc(s).	