

SAIE-M8B-8-0.2U-HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M8 thread, Female socket, straight, Mounting thread: M8, Number of poles: 8, Strand / cable length: 0.2 m
Order No.	1467640000
Type	SAIE-M8B-8-0.2U-HW
GTIN (EAN)	4050118273175
Qty.	1 pc(s).

SAIE-M8B-8-0.2U-HW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	10 g
------------	------

Technical data customisable plug-in connectors

Cable glands	M 8	Coding	none
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Number of poles	8	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	1.5 A
Rated voltage	30 V	Temperature range of housing	-25...+85 °C
Type of connection	Socket connector		

Standards

Connector standard	IEC 61076-2-104
--------------------	-----------------

General data

Cable glands	M 8	Cable length	0.2 m
Coding	none	Conductor O.D.	-
Connection thread	M8 thread	Contact surface	Gold-plated
Core cross-section	0.14 mm ²	Housing main material	Brass, nickel-plated
Mounting thread	M8	Number of poles	8
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	1.5 A	Rated voltage	30 V
Rated voltage	30 V	Strand / cable length	0.2 m
Temperature range of housing	-25...+85 °C	Type of connection	Socket connector
Wire cross section (Print/Online)	0,14 mm ²		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ECLASS 9.0	27-44-01-03	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-03	ECLASS 11.0	27-44-01-03
ECLASS 12.0	27-44-01-03	ECLASS 13.0	27-44-01-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAIE-M8B-8-0.2U-HW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

