

**IE-CC-NM-SMAM-4M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

**Antennas and antenna accessories (coax cables and mounts)**

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Antenna cable, Connection 1: N male, Connection 2: SMA male, Length: 4 m
Order No.	<a href="#">1491190000</a>
Type	IE-CC-NM-SMAM-4M
GTIN (EAN)	4050118300734
Qty.	1 pc(s).

**IE-CC-NM-SMAM-4M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	4 m	Length (inches)	157.48 inch
Net weight	186 g		

**Temperatures**

Storage temperature	-70 °C...85 °C	Operating temperature	-40 °C...85
---------------------	----------------	-----------------------	-------------

**Electrical properties of cable**

Attenuation at 2000 MHz	approx. 0.5 dB/m	Attenuation at 800 MHz	approx. 0.31 dB/m
Characteristic impedance	50 Ω		

**Mechanical and material properties of cable**

Material sheath	Polyethylene	Min. bending radius, once only	12,7 mm
Min. bending radius, repetitive	50,8 mm	Sheath diameter	4.95 mm
UV-resistant	Yes		

**Technical data**

Type of connection	Connection 1: N male, Connection 2: SMA male
--------------------	---

**Environmental conditions**

Operating temperature, max.	85	Operating temperature, min.	-40 °C
Storage temperature, max.	85 °C	Storage temperature, min.	-70 °C

**Classifications**

ETIM 6.0	EC001682	ETIM 7.0	EC001682
ETIM 8.0	EC001682	ETIM 9.0	EC001682
ECLASS 9.0	27-06-03-10	ECLASS 9.1	27-06-03-10
ECLASS 10.0	27-06-03-10	ECLASS 11.0	27-06-03-10
ECLASS 12.0	27-06-03-10	ECLASS 13.0	27-06-03-10

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
------------	----------------

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### IE-CC-NM-SMAM-4M

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Product image



Connection 1: SMA male

### Product image



Connection 2: N-type male