

H1,0/16D R BD GSP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code
- other colour code

General ordering data

| | |
|------------|---|
| Version | Wire-end ferrule, Standard, 12 mm, 10 mm, red |
| Order No. | 1476090000 |
| Type | H1,0/16D R BD GSP |
| GTIN (EAN) | 4050118282924 |
| Qty. | 5,000 pc(s). |
| Packaging | Reel |

H1,0/16D R BD GSP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|---------|
| Net weight | 0.138 g |
|------------|---------|

Technical data

| | | | |
|------------------------|-----------------------------------|---------|----------|
| Description of article | Wire-end ferrules on reel, red | Version | Standard |
|------------------------|-----------------------------------|---------|----------|

Wire-end ferrules

| | | | |
|-----------------------------|-------------------|--|---------|
| Collar diameter (D2) | 3 mm | Colour code | DIN |
| Conductor cross-section | 1 mm ² | Contact surface diameter (D1) | 1.4 mm |
| Contact surface length (L2) | 10 mm | L1 in mm | 16 mm |
| Metal sleeve thickness (S1) | 0.15 mm | Plastic collar thickness (S2) | 0.25 mm |
| Stripping length | 12 mm | Wire connection cross section AWG, max. | AWG 17 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000005 | ETIM 7.0 | EC000005 |
| ETIM 8.0 | EC000005 | ETIM 9.0 | EC000005 |
| ECLASS 9.0 | 27-40-02-01 | ECLASS 9.1 | 27-40-02-01 |
| ECLASS 10.0 | 27-40-02-01 | ECLASS 11.0 | 27-40-02-01 |
| ECLASS 12.0 | 27-40-02-01 | ECLASS 13.0 | 27-40-02-01 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E354986 |

Downloads

| | |
|--------------------|--|
| User Documentation | Technical information - EN Technical information - DE |
| Catalogues | Catalogues in PDF-format |

H1,0/16D R BD GSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

