

STRIPAX ULTIMATE XL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	1512780000
Type	STRIPAX ULTIMATE XL
GTIN (EAN)	4050118319934
Qty.	1 pc(s).

STRIPAX ULTIMATE XL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	22 mm	Depth (inches)	0.866 inch
Height	99 mm	Height (inches)	3.898 inch
Width	190 mm	Width (inches)	7.48 inch
Net weight	171.8 g		

Technical data

Description of article	Wire stripper unit
------------------------	--------------------

Stripping tools

Cable type	Flexible and solid conductors with halogen-free insulation	Conductor cross-section (cutting capacity)	6 mm ²
Conductor cross-section, max.	10 mm ²	Conductor cross-section, min.	2.5 mm ²
Stripping length, max.	25 mm	Stripping range AWG, max.	8 AWG
Stripping range AWG, min.	14 AWG		

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ETIM 9.0	EC002109
ECLASS 9.0	21-04-37-06	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-37-06	ECLASS 11.0	21-04-37-06
ECLASS 12.0	21-04-37-06	ECLASS 13.0	21-04-37-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Downloads

Product Change Notification	Technische Änderung für Abisolierwerkzeug Stripax Technical change to stripping tool Stripax
User Documentation	Manual Library and function block – BDAL Stripax all version
Catalogues	Catalogues in PDF-format
Brochures	

STRIPAX ULTIMATE XL


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Example of use



STRIPAX ULTIMATE XL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories / replacement parts**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

Type	ERME SPX UL XL	Version
Order No.	1512790000	Accessories, Cutter holder
GTIN (EAN)	4050118320428	
Qty.	1 pc(s).	
Type	ERTE KLBC SPX UL XL	Version
Order No.	2571510000	Accessories, Replacement clamping jaw
GTIN (EAN)	4050118581997	
Qty.	1 pc(s).	