


**CC-H 85/54 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	ClipCard, Accessories, 90 x 58 mm, dark beige
Order No.	<a href="#">1631640003</a>
Type	CC-H 85/54 BG
GTIN (EAN)	4008190465292
Qty.	20 pc(s).

**CC-H 85/54 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	13 mm	Depth (inches)	0.512 inch
Height	90 mm	Height (inches)	3.543 inch
Width	58 mm	Width (inches)	2.283 inch
Net weight	25.15 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Colour	dark beige	
Halogen	No	
Material	Polyamide 66	
Number of markers per combination	1 MultiCard = Accessories	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-40... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Width	58 mm	

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**CC-H 85/54 BG****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Natural**

CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

**General ordering data**

Type	CB 365/7,5 NC	Version
Order No.	<a href="#">1279100000</a>	Cable ties, 7.5 x 365 mm, Polyamide 66, 540 N
GTIN (EAN)	4008190104665	
Qty.	100 pc(s).	
Type	CB 360/4,5 NC	Version
Order No.	<a href="#">1279000000</a>	Cable ties, 4.5 x 360 mm, Polyamide 66, 220 N
GTIN (EAN)	4008190031459	
Qty.	100 pc(s).	