

**LM MT300 60/36 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

Version	LaserMark, Device markers, 36 x 60 mm, silver
Order No.	<a href="#">1686430001</a>
Type	LM MT300 60/36 SI
GTIN (EAN)	4008190494124
Qty.	10 pc(s).

## LM MT300 60/36 SI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	36 mm	Height (inches)	1.417 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	11.6 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	silver		
Halogen	No		
Material	Polyester, PVC-free		
Number of markers per combination	1 Label sheet = 21 Device markers		
Number of markers per packaging unit	Number of markers per combination	21	
	Number of combinations per packaging unit	10	
	Form of supply	Label sheet	
Number of markers per packaging unit	210		
Number per sheet	21		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printing method	Laser print		
UL 94 flammability rating	HB		
Version	Self-adhesive		
Width	60 mm		

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

ROHS	Conform
------	---------

### LM MT300 60/36 SI

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**LM MT300 60/36 SI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

