

LM MT300 210/297 SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 297 x 210 mm, silver
Order No.	1686440001
Type	LM MT300 210/297 SI
GTIN (EAN)	4008190494162
Qty.	10 pc(s).

LM MT300 210/297 SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	297 mm	Height (inches)	11.693 inch
Width	210 mm	Width (inches)	8.268 inch
Net weight	12.3 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	silver		
Halogen	No		
Material	Polyester, PVC-free		
Number of markers per combination	1 Label sheet = 1 Device markers		
Number of markers per packaging unit	Number of combinations per packaging unit	10	
	Form of supply	Label sheet	
	Number of markers per combination	1	
Number of markers per packaging unit	10		
Number per sheet	1		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printing method	Laser print		
UL 94 flammability rating	HB		
Version	Self-adhesive		
Width	210 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

LM MT300 210/297 SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

LM MT300 210/297 SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

