

TABPACK 15X6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

TabPack consists of blank labels in a handy format for marking in situ with a felt-tip pen or a ballpoint pen.

General ordering data

Version	Device markers, Device markers, 6 x 15 mm, yellow
Order No.	1686120000
Type	TABPACK 15X6
GTIN (EAN)	4008190492427
Qty.	1 pc(s).

TABPACK 15X6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	6 mm	Height (inches)	0.236 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	33 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Permanent acrylic copolymer	
Approval acc. to UL 969	No	
Colour	yellow	
Halogen	No	
Material	Acrylic-coated fibre webbing	
Material colour according to resistance code	4	
Number of markers per combination	1 Label sheet = 100 Device markers	
Number of markers per packaging unit	1,000	
Number of markers per packaging unit	Form of supply	Label sheet
	Number of markers per combination	100
	Number of combinations per packaging unit	10
Number per sheet	100	
Operating temperature range	-29...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-29 °C	
Version	Self-adhesive	
Width	15 mm	

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

TABPACK 15X6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Catalogues

[Catalogues in PDF-format](#)