

DFFC .5-1.0 ZRV1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

| | |
|------------|---|
| Version | Crimp contact (terminal), 1.5 mm ² |
| Order No. | 1705320000 |
| Type | DFFC .5-1.0 ZRV1.5 |
| GTIN (EAN) | 4008190948566 |
| Qty. | 500 pc(s). |

DFFC .5-1.0 ZRV1.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

| | |
|------------|--------|
| Net weight | 0.22 g |
|------------|--------|

Material data

| | | | |
|----------|---------|--------|--------|
| Material | Plastic | Colour | silver |
|----------|---------|--------|--------|

System specifications

| | |
|---------|---|
| Version | for holding 0.5 ... 1.0 mm ² |
|---------|---|

Additional technical data

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Conductors for clamping (rated connection)

| | |
|--------------------|---------------|
| Type of connection | Crimp contact |
|--------------------|---------------|

General

| | |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

Rating data

| | | | |
|---|---------------------|--|---------|
| Rated cross-section | 1.5 mm ² | Volume resistance according to IEC 60947-7-x | 1.83 mΩ |
| Power loss in accordance with IEC 60947-7-x | 0.56 W | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000796 | ETIM 7.0 | EC000796 |
| ETIM 8.0 | EC000796 | ETIM 9.0 | EC000796 |
| ECLASS 9.0 | 27-44-02-04 | ECLASS 9.1 | 27-44-02-04 |
| ECLASS 10.0 | 27-44-02-04 | ECLASS 11.0 | 27-44-02-04 |
| ECLASS 12.0 | 27-44-02-04 | ECLASS 13.0 | 27-44-02-04 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | StorageConditionsTerminalBlocks |
| Catalogues | Catalogues in PDF-format |
| Brochures | CAT 1 TERM 16/17 EN |