

LM MT300 25.4/12.7 SI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

General ordering data

Version	LaserMark, Device markers, 12.7 x 25.4 mm, silver
Order No.	1686390001
Type	LM MT300 25.4/12.7 SI
GTIN (EAN)	4008190493967
Qty.	10 pc(s).

LM MT300 25.4/12.7 SI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	12.7 mm	Height (inches)	0.5 inch
Width	25.4 mm	Width (inches)	1 inch
Net weight	11.8 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	silver		
Halogen	No		
Material	Polyester, PVC-free		
Number of markers per combination	1 Label sheet = 147 Device markers		
Number of markers per packaging unit	Number of combinations per packaging unit	10	
	Number of markers per combination	147	
	Form of supply	Label sheet	
Number of markers per packaging unit	1,470		
Number per sheet	147		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printing method	Laser print		
UL 94 flammability rating	HB		
Version	Self-adhesive		
Width	25.4 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Environmental Product Compliance

REACH SVHC	/
------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

Creation date July 4, 2024 5:19:13 PM CEST

Catalogue status 29.06.2024 / We reserve the right to make technical changes.

LM MT300 25.4/12.7 SI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

