

KLBUE 10-20 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

The shield clamping saddles for direct mounting can be easily and conveniently attached directly to the mounting plate. The products differ in the range of the cable diameter and the thread for fastening the shield clamping saddles.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1712321001
Type	KLBUE 10-20 SC
GTIN (EAN)	4032248032341
Qty.	10 pc(s).

KLBUE 10-20 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	40 mm	Depth (inches)	1.575 inch
Height	26 mm	Height (inches)	1.024 inch
Width	23.6 mm	Width (inches)	0.929 inch
Mounting dimension - width	22.1 mm	Net weight	31.948 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Snap-on	Type of mounting	Screw

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

Dimensions

Length of thread	5.3 mm	Pitch in mm (P)	30 mm
------------------	--------	-----------------	-------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Beipackzettel_KLBUE.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

KLBUE 10-20 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Tools**

Our special tools support within the cabinet process in the area of wiring or also the assembly of the components.

General ordering data

Type	BTWZ KLBUE	Version
Order No.	1742630000	Tools, Operating tool
GTIN (EAN)	4008190980764	
Qty.	1 pc(s).	