

SKMU M20 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|--|
| Version | SKMU MS (brass locknut), Locknut, M 20, 3 mm, Brass, nickel-plated |
| Order No. | 1737000000 |
| Type | SKMU M20 MS |
| GTIN (EAN) | 4008190956479 |
| Qty. | 100 pc(s). |

SKMU M20 MS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 3 mm | Height (inches) | 0.118 inch |
| Net weight | 2.45 g | | |

General information

| | | | |
|-----------------|----------------------|------------------|----------|
| AF size 1 | 24 mm | Cable glands | M 20 |
| External thread | M 20 | Halogen | No |
| Internal thread | M 20 | Length of thread | 3 mm |
| Material | Brass, nickel-plated | O.D. | 26.56 mm |
| Pitch of thread | 1.5 mm | Thickness | 3 mm |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000940 | ETIM 7.0 | EC000940 |
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ECLASS 9.0 | 27-14-44-24 | ECLASS 9.1 | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-05 | ECLASS 13.0 | 27-14-08-05 |

Environmental Product Compliance

| | |
|--------------------------------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | f350dea6-3de1-42c5-a935-c4eb3e9d5e3c |
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 6c |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

SKMU M20 MS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

