

**VG 21-K68 SKS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG K SZS (standard plastic cable gland with anti-kink coils), Cable glands, straight, PG 21, 11 mm, OD min. 13 - OD max. 18 mm, Polyamide 6
Order No.	<a href="#">1720520000</a>
Type	VG 21-K68 SKS
GTIN (EAN)	4008190358730
Qty.	20 pc(s).

**VG 21-K68 SKS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	119 mm	Height (inches)	4.685 inch
Length	130 mm	Length (inches)	5.118 inch
Net weight	32.15 g		

**Temperatures**

Operating temperature	-20 °C...100 °C
-----------------------	-----------------

**Certificate numbers cable gland**

Certificate no. cable gland (cULus)	E140310
-------------------------------------	---------

**General information**

AF size	33 mm	AF size 1	33 mm
Cable glands	PG	External thread	PG 21
Halogen	Yes	Length of thread	11 mm
Material	Polyamide 6	Operating temperature range, max.	100 °C
Operating temperature range, min.	-20 °C	Outer cable diameter, max.	18 mm
Outer cable diameter, min.	13 mm	Pitch of thread	1.59 mm
Protection degree	IP68 - 5 bar (30 min.)	Seal insert	CR
Silicone	No	Tightening torque	8 Nm
Torque for cap nut, max.	6 Nm	Torque for cap nut, min.	5 Nm
Torque for connecting adapter, max.	9 Nm	Torque for connecting adapter, min.	7 Nm
UL 94 flammability rating	V-2		

**Classifications**

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

Approvals



ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

## VG 21-K68 SKS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Plastic lock nuts, grey



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU PG21-K GR	Version
Order No.	<a href="#">1698220000</a>	SKMU PA (plastic locknut), Locknut, PG 21, 7 mm, Polyamid 6 (PA6 -
GTIN (EAN)	4008190884758	GF30)
Qty.	100 pc(s).	

## Neoprene flat gasket - GWDR NP



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	GWDR PG21-NP	Version
Order No.	<a href="#">1719590000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, PG 21, Neoprene
GTIN (EAN)	4008190352851	
Qty.	100 pc(s).	

**VG 21-K68 SKS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR PG2 1-PO	Version
Order No.	<a href="#">1719490000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, PG 21,
GTIN (EAN)	4008190352752	Polyethylene
Qty.	100 pc(s).	