

**LM MT300 18/6.5 SI****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

Version	LaserMark, Device markers, 6.5 x 18 mm, silver
Order No.	<a href="#">1749320001</a>
Type	LM MT300 18/6.5 SI
GTIN (EAN)	4008190051426
Qty.	10 pc(s).

## LM MT300 18/6.5 SI

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	6.5 mm	Height (inches)	0.256 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	10.8 g		

## Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

## General data

Adhesive	Acrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	silver		
Halogen	No		
Material	Polyester, PVC-free		
Number of markers per combination	1 Label sheet = 320 Device markers		
Number of markers per packaging unit	Number of markers per combination	320	
	Form of supply	Label sheet	
	Number of combinations per packaging unit	10	
Number of markers per packaging unit	3,200		
Number per sheet	320		
Operating temperature range	-40...150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printing method	Laser print		
UL 94 flammability rating	HB		
Version	Self-adhesive		
Width	18 mm		

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

## Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

## Approvals

ROHS	Conform
------	---------

### LM MT300 18/6.5 SI

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data

[CAD data – STEP](#)

Catalogues

[Catalogues in PDF-format](#)

**LM MT300 18/6.5 SI**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

Drawings

