

THM MT30X 26/10 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

General ordering data

Version	THM, Device markers, 10 x 26 mm, white
Order No.	1751761044
Type	THM MT30X 26/10 WS
GTIN (EAN)	4032248001422
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM MT30X 26/10 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	10 mm	Height (inches)	0.394 inch
Width	26 mm	Width (inches)	1.024 inch
Net weight	479 g		

Temperatures

Operating temperature range	-40...150 °C
-----------------------------	--------------

General data

Adhesive	Acrylate adhesive		
Approval acc. to UL 969	Yes		
Colour	white		
Halogen	No		
Material	Polyester		
Material colour according to resistance code	9		
Number of markers per combination	1 Label reel = Device markers		
Number of markers per packaging unit	Form of supply	Label reel	
Number per roll	10,000		
Operating temperature range	-40... 150 °C		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Printing method	Thermal transfer		
UL 94 flammability rating	V-0		
Version	Self-adhesive, halogen-free		
Width	26 mm		

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

THM MT30X 26/10 WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM MT30X 26/10 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	