

**CC-RAIL 1000****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

Version	ClipCard, Accessories, 1000 x 17 mm, Self-adhesive, black
Order No.	<a href="#">1790150000</a>
Type	CC-RAIL 1000
GTIN (EAN)	4032248213610
Qty.	1 pc(s).

**CC-RAIL 1000****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	6 mm	Depth (inches)	0.236 inch
Height	1,000 mm	Height (inches)	39.37 inch
Width	17 mm	Width (inches)	0.669 inch
Net weight	10 g		

**Temperatures**

Operating temperature range	-20...80 °C
-----------------------------	-------------

**General data**

Adhesive	Double-sided adhesive tape	
Application/manufacturer	Self-adhesive	
Colour	black	
Halogen	No	
Material	PVC	
Number of markers per combination	1 MultiCard = Accessories	
Number of markers per packaging unit	Form of supply	MultiCard
Operating temperature range	-20...80 °C	
Operating temperature range, max.	80 °C	
Operating temperature range, min.	-20 °C	
UL 94 flammability rating	V-0	
Version	Self-adhesive	
Width	17 mm	

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04
ECLASS 14.0	27-28-11-04		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

### CC-RAIL 1000

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

