

HDC-KIT-HE 48.150 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element.

All screw connections are equipped with a wire protection spring.

Screw connection

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Size: 12, Poles: 48, Screw connection, 500 V, 16 A, diecast aluminium, M 40
Order No.	1802360000
Type	HDC-KIT-HE 48.150 M
GTIN (EAN)	4032248256815
Qty.	1 pc(s).

HDC-KIT-HE 48.150 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	2,130.68 g
------------	------------

Temperatures

Limit temperature	-40 °C ... 100 °C
-------------------	-------------------

General data

BG	12	Cable glands	M 40
Connection type PE	Screw connection	Material	diecast aluminium
Number of poles	48	Rated current (DIN EN 61984)	16 A
Rated voltage (DIN EN 61984)	500 V	Series	HE
Size	12		

Version

BG	12	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Material	diecast aluminium
Max. torque for main contact	0.55 Nm	Min. torque for main contact	0.5 Nm
Size	12	Surface finish	Powder coating
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-01-90
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92
ECLASS 14.0	27-44-02-92		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076
RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6bl, 6c

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

HDC-KIT-HE 48.150 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****SPB**

Various accessories are available for our inserts. This includes coding elements for the inserts.

General ordering data

Type	SPB-M 3	Version
Order No.	1203600000	Heavy-duty connectors, Accessories, Lock bolts
GTIN (EAN)	4008190120047	
Qty.	100 pc(s).	

HDC COS

Various accessories are available for our inserts. This includes coding elements for the inserts.

General ordering data

Type	HDC COS 24	Version
Order No.	1430900000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190077228	
Qty.	1 pc(s).	
Type	HDC COS 32	Version
Order No.	1430800000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190176181	
Qty.	1 pc(s).	
Type	HDC COS 16	Version
Order No.	1431000000	Heavy-duty connectors, Accessories, Coding System
GTIN (EAN)	4008190052706	
Qty.	1 pc(s).	