

**WQL 3 WF6-10/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Reducing cross-connectors enable simple and fast connection of terminal blocks with different rated cross-sections.

**General ordering data**

Version	Bolt-type screw terminals, Cross-connector, Number of poles: 3
Order No.	<a href="#">1806640000</a>
Type	WQL 3 WF6-10/2
GTIN (EAN)	4032248294695
Qty.	5 pc(s).

**WQL 3 WF6-10/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	4 mm	Depth (inches)	0.157 inch
Height	82 mm	Height (inches)	3.228 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	57.4 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Copper - zinc	Colour	grey
----------	---------------	--------	------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Conductors for clamping (additional connection)**

Terminal screw, additional connection	M 10
---------------------------------------	------

**Conductors for clamping (rated connection)**

Clamping screw	M 6
----------------	-----

**Cross-connector**

Number of cross-connected terminals	3	Rated current, 2-pole	269 A
Rated current, multi-pole	125 A	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	22 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	269 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

**Environmental Product Compliance**

REACH SVHC	/
------------	---

## WQL 3 WF6-10/2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	