

TM 205/15 V0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Our extensive range of TM sleeves is suitable for all-purpose use. They cover a wide range of applications: from thin conductors to cables with large external diameters. This range offers printed inlay tags with maximum protection against outside influences. TM sleeves permit flexible installation.

- Optimum protection for printed inlay tags
- Wide range of applications for conductors and cables
- One tag type for all cross-sections
- TMX 30 for mounting with cable ties (width 4.6 mm)

General ordering data

Version	TM, Socket x 18 mm, PVC, Colour: Transparent, Conductor O.D.: 10 - 14 mm
Order No.	1806250000
Type	TM 205/15 V0
GTIN (EAN)	4032248275762
Qty.	200 pc(s).

TM 205/15 V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	15 mm	Height (inches)	0.591 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	0.89 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Colour	Transparent	Material	PVC
Operating temperature range	-40...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-40 °C	Recommended industries	Transportation, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Width	18 mm		

Conductor and cable markers

Conductor O.D.	10 - 14 mm	Conductor O.D., max.	14 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	35 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 35 mm ²

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	Zuken E3.S
Product Change Notification	PCN Transparent Sleeves_DE PCN Transparent Sleeves_EN
Catalogues	Catalogues in PDF-format

TM 205/15 V0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Blank



TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 15 MC NE VI	Version
Order No.	1427870000	TM-I, Insert markers, 15 x 4 mm, violet
GTIN (EAN)	4050118231847	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE SI	Version
Order No.	1609981697	TM-I, Insert markers, 15 x 4 mm, silver
GTIN (EAN)	4008190137410	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE GE	Version
Order No.	1609981687	TM-I, Insert markers, 15 x 4 mm, yellow
GTIN (EAN)	4008190914776	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE RT	Version
Order No.	1609981686	TM-I, Insert markers, 15 x 4 mm, red
GTIN (EAN)	4008190367824	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE WS	Version
Order No.	1609981044	TM-I, Insert markers, 15 x 4 mm, white
GTIN (EAN)	4008190914783	
Qty.	400 pc(s).	
Type	TM-I 15 MC NE BL	Version
Order No.	1609981693	TM-I, Insert markers, 15 x 4 mm, blue
GTIN (EAN)	4008190367831	
Qty.	400 pc(s).	

TM 205/15 V0

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	TM-I 15 MC NE GN	Version
Order No.	1609981688	TM-I, Insert markers, 15 x 4 mm, green
GTIN (EAN)	4008190398705	
Qty.	400 pc(s).	