

**ZB 4K GG HENSEL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Bus bar taps with insulation offer finger safety on the one hand. On the other hand, the colored insulation also indicates the respective potential, such as the neutral conductor or PE.

**General ordering data**

Version	Clamping yoke (bus-bar)
Order No.	<a href="#">1824560000</a>
Type	ZB 4K GG HENSEL
GTIN (EAN)	4032248330973
Qty.	50 pc(s).

**ZB 4K GG HENSEL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	20.4 mm	Depth (inches)	0.803 inch
Height	19 mm	Height (inches)	0.748 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	3.86 g		

**Material data**

Material	Steel	Insulating material	PA
Colour	silver		

**Rating data IECEx/ATEX**

Safety notice	<p>Installation instructions: The potential equalisation (PE) rail modules are suitable for use in housings in atmospheres with flammable gases and dust. For use in areas with flammable gases, these housings must meet the requirements of EN 60079-0 and EN 60079-7. For use in areas with flammable dust, these housings must meet the requirements of EN 60079-0 and EN 60079-31.</p> <p>When combined with other terminal block ranges and sizes, and when other accessories are used, you must comply with the clearance and creepage distances given.</p> <p>Regarding accessory use, the manufacturer's instructions must be followed.</p> <p>List of restrictions: The PE rail modules are considered one component, with Ex marking when used with the busbar holders of type SH and WEW. When used independently, the above named components are not covered by this certificate.</p>
---------------	--

**System specifications**

Version	for busbar 10 x 3 mm
---------	----------------------

**Additional technical data**

Installation advice	Feed-through (bushing)	Type of mounting	when screwed in
---------------------	------------------------	------------------	-----------------

**ZB 4K GG HENSEL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Conductors for clamping (rated connection)**

Type of connection	Clamping yoke
--------------------	---------------

**General**

Installation advice	Feed-through (bushing)
---------------------	------------------------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-46
ECLASS 12.0	27-14-11-46	ECLASS 13.0	27-25-01-16

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>