

**WQV 95N/120N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Silver grey, 269 A, Number of poles: 3, Pitch in mm (P): 27.00, Insulated: No, Width: 9.5 mm
Order No.	<a href="#">1826900000</a>
Type	WQV 95N/120N/3
GTIN (EAN)	4032248329953
Qty.	5 pc(s).

**WQV 95N/120N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	29 mm	Depth (inches)	1.142 inch
Height	64 mm	Height (inches)	2.52 inch
Width	9.5 mm	Width (inches)	0.374 inch
Net weight	77 g		

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

**System specifications**

Version	For the terminals
---------	-------------------

**Additional technical data**

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

**Cross-connector**

Number of cross-connected terminals	3	Rated current, multi-pole	269 A
Tightening torque range for fixing screw	3.0...6.0 Nm	Type	Cross-connector

**Dimensions**

Pitch in mm (P)	27 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Number of poles	3
---------------------	-----------------	-----------------	---

**Rating data**

Rated current	269 A
---------------	-------

**Classifications**

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03
ECLASS 14.0	27-25-03-03		

**Environmental Product Compliance**

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

**WQV 95N/120N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

ROHS

Conform

**Downloads**

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)  
[Instruction](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

**WQV 95N/120N/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Distance sleeve****General ordering data**

Type	VH 36.1/8/6.4	Version
Order No.	<a href="#">1967100000</a>	W-Series, Spacer sleeve
GTIN (EAN)	4032248739202	
Qty.	5 pc(s).	