

**WQV 95N/120N/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 4, Pitch in mm (P): 27.00, Insulated: No, 269 A, Silver grey
Order No.	<a href="#">1826910000</a>
Type	WQV 95N/120N/4
GTIN (EAN)	4032248329960
Qty.	5 pc(s).

## WQV 95N/120N/4

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	29 mm	Depth (inches)	1.142 inch
Height	91 mm	Height (inches)	3.583 inch
Width	9.5 mm	Width (inches)	0.374 inch
Net weight	106 g		

## Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

## Material data

Material	tinned copper	Colour	Silver grey
----------	---------------	--------	-------------

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	when screwed in
---------------------	-----------------	----------------	-----------------

## Cross-connector

Number of cross-connected terminals	4	Rated current, multi-pole	269 A
Tightening torque range for fixing screw	3.0...6.0 Nm	Type	Cross-connector

## Dimensions

Pitch in mm (P)	27 mm
-----------------	-------

## General

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

## Rating data

Rated current	269 A
---------------	-------

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Environmental Product Compliance

REACH SVHC	/
------------	---

## Approvals

ROHS	Conform
------	---------

## WQV 95N/120N/4

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a> <a href="#">Instruction</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**WQV 95N/120N/4****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Distance sleeve****General ordering data**

Type	VH 36.1/8/6.4	Version
Order No.	<a href="#">1967100000</a>	W-Series, Spacer sleeve
GTIN (EAN)	4032248739202	
Qty.	5 pc(s).	