

SAIB-VSA-3P/24/9/LD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

General ordering data

Version	Valve plug-in connector (field assembled), Number of poles: 3, Design A (18 mm), Free-wheel diode, 24 V, 0.34...1.5 mm ²
Order No.	1873120000
Type	SAIB-VSA-3P/24/9/LD
GTIN (EAN)	4032248495399
Qty.	1 pc(s).

SAIB-VSA-3P/24/9/LD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	25 g
------------	------

Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits		Free-wheel diode	Cable diameter, max.	8 mm
Cable diameter, min.	6 mm		Cable glands	PG 9
Coding	Design A (18 mm)		Conductor cross-section, max.	1.5 mm ²
Conductor cross-section, min.	0.34 mm ²		Connection cross-section, max.	1.5 mm ²
Connection cross-section, min.	0.34 mm ²		Contact surface	Ni
Housing main material	PA 6 GF		Insulation strength	10 ⁸ Ω
LED	Yes		Number of poles	3
Plugging cycles	≤ 50		Pollution severity	3
Protection degree	IP65		Rated current	10 A
Rated voltage	24 V		Temperature range of housing	-25...+85 °C
Type of connection	Screw connection			

Classifications

ETIM 6.0	EC002062	ETIM 7.0	EC003623
ETIM 8.0	EC003623	ETIM 9.0	EC003623
ECLASS 9.0	27-44-01-05	ECLASS 9.1	27-44-01-05
ECLASS 10.0	27-44-01-05	ECLASS 11.0	27-44-01-05
ECLASS 12.0	27-44-01-05	ECLASS 13.0	27-44-01-05
ECLASS 14.0	27-44-01-05		

Environmental Product Compliance

REACH SVHC	/
RoHS Compliance Status	Compliant without exemption

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN


SAIB-VSA-3P/24/9/LD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany


www.weidmueller.com

Drawings

Dimensioned drawing



Pole scheme



Wiring diagram

