

SAIB-ZW-MT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. In special-purpose machine engineering, certain applications require two different lengths of cables which are routed to a single plug-in. To resolve this problem, we offer customisable male plugs and female sockets with two cable outlets. The miniature twin plug comes with a 90° outlet and a straight outlet. The angled version can be rotated as required at 90° intervals.

General ordering data

Version	Field attachable connector, M12, Female socket, straight
Order No.	1878490000
Type	SAIB-ZW-MT
GTIN (EAN)	4032248471225
Qty.	1 pc(s).

SAIB-ZW-MT

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	36 g
------------	------

Technical data customisable plug-in connectors

Cable diameter	1...3 mm, 4...5 mm	Coding	A-coded
Conductor cross-section, max.	0.75 mm ²	Conductor cross-section, min.	0.14 mm ²
Contact surface	CuSnZn	Housing main material	PA
Number of poles	5	Pollution severity	3
Protection degree	IP67	Rated current	4 A
Rated voltage	36 V	Shield connection	No
Temperature range of housing	-25...+85 °C	Threaded ring material	Diecast zinc
Type of connection	Screw connection		

General Info

Number of poles	5	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact surface	CuSnZn
Protection degree	IP67		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC002635
ETIM 8.0	EC002635	ETIM 9.0	EC002635
ECLASS 9.0	27-44-01-02	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-02	ECLASS 11.0	27-44-01-02
ECLASS 12.0	27-44-01-16	ECLASS 13.0	27-44-01-02
ECLASS 14.0	27-44-01-16		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4
RoHS Compliance Status	Compliant

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E307231

Downloads

Engineering Data	CAD data – STEP
User Documentation	Manual
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

SAIB-ZW-MT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Pole scheme

