

TS 35X15/5X18 2M/ST/SZ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

General ordering data

Version	Terminal rail, with slot, Accessories, 35 x 15 x 2000 mm, Slit width: 5.20 mm, Slit length: 18.00 mm, Steel, galvanic zinc plated and passivated
Order No.	1879100000
Type	TS 35X15/5X18 2M/ST/SZ
GTIN (EAN)	4032248473793
Qty.	2 m

TS 35X15/5X18 2M/ST/SZ**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	15 mm	Depth (inches)	0.591 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2,000 mm	Width (inches)	78.74 inch
Net weight	620 g		

Mounting rail

Installation advice	Direct mounting	
Length of the terminal rail	nominal	2,000 mm
	min.	0 mm
	max.	2,000 mm
Material	Steel	
Pre-punched mounting rail	Yes	
Short circuit strength corresponds to E-Cu wire	50 mm ²	
Short-time withstand current per second 6 kA according to IEC 60947-7-2		
Slit gap	7 mm	
Slit gap		
Slit length	18 mm	
Slit length		
Slit width	5.2 mm	
Slit width		
Standards	In accordance with DIN EN 60715	
Surface finish	galvanic zinc plated and passivated	

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

Important note

Product information	Din rails with Sendzimir treatment have limited corrosion resistance on the outer and cut edges
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	Storage Conditions Terminal Blocks
Catalogues	Catalogues in PDF-format



TS 35X15/5X18 2M/ST/SZ

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Product image



Similar to illustration