

**ETO CC 15/49 TRANSPAR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

**General ordering data**

Version	ClipCard, Accessories, 15 x 49 mm, Transparent
Order No.	<a href="#">1880830000</a>
Type	ETO CC 15/49 TRANSPAR.
GTIN (EAN)	4032248480906
Qty.	10 pc(s).

**ETO CC 15/49 TRANSPAR.****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	1 mm	Depth (inches)	0.039 inch
Height	15 mm	Height (inches)	0.591 inch
Width	49 mm	Width (inches)	1.929 inch
Net weight	11.7 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**General data**

Adhesive	Permanent acrylic copolymer	
Colour	Transparent	
Halogen	No	
Material	Polyester film	
Number of markers per combination	1 MultiCard = Accessories	
Number of markers per packaging unit	Form of supply	MultiCard
Number per sheet	76	
Operating temperature range	-40... 100 °C	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-40 °C	
Recommended industries	Machinery	
UL 94 flammability rating	V-2	
Width	49 mm	

**Device markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ETIM 9.0	EC001288
ECLASS 9.0	27-40-06-29	ECLASS 9.1	27-40-06-29
ECLASS 10.0	27-40-06-29	ECLASS 11.0	27-28-11-04
ECLASS 12.0	27-28-11-04	ECLASS 13.0	27-28-11-04

**Environmental Product Compliance**

REACH SVHC	/
------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

**ETO CC 15/49 TRANSPAR.**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

