

**WAP 2.5-10/0.5MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

Version	End plate (terminals), dark beige, Height: 54.5 mm, Width: 0.35 mm, V-O, Wemid
Order No.	<a href="#">1966380000</a>
Type	WAP 2.5-10/0.5MM
GTIN (EAN)	4032248688616
Qty.	50 pc(s).

**WAP 2.5-10/0.5MM****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	49 mm	Depth (inches)	1.929 inch
Height	54.5 mm	Height (inches)	2.146 inch
Width	0.35 mm	Width (inches)	0.014 inch
Net weight	1.64 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

**Material data**

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

**System specifications**

Version	End plate
---------	-----------

**Additional technical data**

Installation advice	Feed-through (bushing)	Snap-on	Yes
---------------------	------------------------	---------	-----

**Dimensions**

TS 35 offset	28 mm
--------------	-------

**General**

Installation advice	Feed-through (bushing)
---------------------	------------------------

**Classifications**

ETIM 6.0	EC000886	ETIM 7.0	EC000886
ETIM 8.0	EC000886	ETIM 9.0	EC000886
ECLASS 9.1	27-14-11-33	ECLASS 10.0	27-14-11-33
ECLASS 11.0	27-14-11-33	ECLASS 12.0	27-14-11-33
ECLASS 13.0	27-25-03-01	ECLASS 14.0	27-25-03-01

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals**

ROHS	Conform
------	---------

### WAP 2.5-10/0.5MM

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Con-  
formity

[Confirmation of Standards EN 45545-2\\_2020-10](#)

Engineering Data

[CAD data – STEP](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)