

SAIE-M8B-4-2.5U-FP-M8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M8 thread, Female socket, straight, Mounting thread: M8, Number of poles: 4, Strand / cable length: 2.5 m
Order No.	1985400000
Type	SAIE-M8B-4-2.5U-FP-M8
GTIN (EAN)	4050118369854
Qty.	1 pc(s).

SAIE-M8B-4-2.5U-FP-M8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	45 g
------------	------

Technical data customisable plug-in connectors

Cable glands	M 8	Coding	none
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Number of poles	4	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Type of connection	Socket connector

Standards

Connector standard	IEC 61076-2-104
--------------------	-----------------

General data

Cable glands	M 8	Cable length	2.5 m
Coding	none	Conductor O.D.	-
Connection thread	M8 thread	Contact surface	Gold-plated
Housing main material	Brass, nickel-plated	Mounting thread	M8
Number of poles	4	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Strand / cable length	2.5 m
Type of connection	Socket connector		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ETIM 9.0	EC003570
ECLASS 9.0	27-44-01-03	ECLASS 9.1	27-44-01-03
ECLASS 10.0	27-44-01-03	ECLASS 11.0	27-44-01-03
ECLASS 12.0	27-44-01-03	ECLASS 13.0	27-44-01-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN

Creation date June 5, 2024 2:52:59 AM CEST

Catalogue status 01.06.2024 / We reserve the right to make technical changes.

SAIE-M8B-4-2.5U-FP-M8

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Wiring diagram



Pole scheme

