

**ZQV 1.5N/9 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

|            |   |
|------------|---|
| Version    | Cross-connector (terminal), Plugged, Number of poles: 9, Pitch in mm (P): 3.50, Insulated: Yes, 17.5 A, red |
| Order No.  | <a href="#">1985790000</a>  |
| Type       | ZQV 1.5N/9 RD   |
| GTIN (EAN) | 4050118370386   |
| Qty.       | 20 pc(s).   |

**ZQV 1.5N/9 RD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 2.8 mm  | Depth (inches)  | 0.11 inch  |
| Height     | 21.9 mm | Height (inches) | 0.862 inch |
| Width      | 30 mm   | Width (inches)  | 1.181 inch |
| Net weight | 2.839 g |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Material data**

|                           |       |        |     |
|---------------------------|-------|--------|-----|
| Material                  | Wemid | Colour | red |
| UL 94 flammability rating | V-0   |        |     |

**Additional technical data**

|                          |     |                |         |
|--------------------------|-----|----------------|---------|
| Explosion-tested version | Yes | Type of fixing | Plugged |
|--------------------------|-----|----------------|---------|

**Cross-connector**

|                       |        |                           |        |
|-----------------------|--------|---------------------------|--------|
| Rated current, 2-pole | 17.5 A | Rated current, multi-pole | 17.5 A |
|-----------------------|--------|---------------------------|--------|

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 3.5 mm |
|-----------------|--------|

**General**

|                 |   |
|-----------------|---|
| Number of poles | 9 |
|-----------------|---|

**Rating data**

|               |        |
|---------------|--------|
| Rated current | 17.5 A |
|---------------|--------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ETIM 9.0    | EC000489    |
| ECLASS 9.0  | 27-14-11-40 | ECLASS 9.1  | 27-14-11-40 |
| ECLASS 10.0 | 27-14-11-40 | ECLASS 11.0 | 27-14-11-40 |
| ECLASS 12.0 | 27-14-11-40 | ECLASS 13.0 | 27-25-03-03 |

**Environmental Product Compliance**

|            |   |
|------------|---|
| REACH SVHC | / |
|------------|---|

**Important note**

|                     |   |
|---------------------|---|
| Product information | Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used |
|---------------------|---|

## ZQV 1.5N/9 RD

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

|   |  |
|---|--|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a>   |
| Engineering Data                            | <a href="#">CAD data – STEP</a>  |
| Engineering Data                            | <a href="#">Zuken E3.S</a>   |
| User Documentation                          | <a href="#">2434520000_BED-ANL_ZQV_A_REIHE.pdf</a><br><a href="#">StorageConditionsTerminalBlocks</a><br><a href="#">User Manual ZQV 2.5</a> |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>   |